




slice[™]
fabriqué

CORDLESS FABRIC CUTTER[™]

QUICK START GUIDE

STEP 1 - PREP CUTTING MAT

1. Apply a line of adhesive to one end of glass mat.
2. Spread a thin coat across entire glass mat with foam brush.
3. Allow adhesive to dry for 2 minutes.



STEP 1, # 1 & 2


STEP 2 - FUSIBLE WEB

1. Cut fabric down to 12" x 12" to make it more manageable.
2. Iron the rough side of fusible web to the back side of fabric using a hot iron, no steam.

* For best results when cutting fabric with Slice[™] Fabriqué, use Slice[™] Fusible Web (sold separately)

STEP 3 - POSITION FABRIC

1. Place fabric directly on glass mat in desired position, fabric side up.
2. Gently smooth fabric with hand until fabric is flat.



STEP 3, # 1 & 2

STEP 4 - INSERT DESIGN CARD


1. Insert design card, label side up, into back slot of Slice[™] Fabriqué.




STEP 4, # 1

STEP 5 - TURN SLICE[™] FABRIQUÉ ON

1. Plug Slice[™] Fabriqué into an electrical outlet.
2. Turn power on by pressing small button on back of Slice[™] Fabriqué.




STEP 5, # 1




STEP 5, # 2

STEP 6 - SELECT SHAPE & SIZE

1. Use single arrows to navigate through designs on screen and double arrows to navigate through pages. Press SELECT to choose shape.
2. After design is chosen, use single arrows to choose size & press SELECT.



STEP 6, # 1




STEP 6, # 2

STEP 7 - CUT DESIGN

1. Press cut button on side of Slice[™] Fabriqué to begin cutting.
2. Gently hold Slice[™] Fabriqué until check mark appears indicating design cut is complete.
3. Lift Slice[™] Fabriqué from mat & remove cut design.



STEP 7, # 1



STEP 7, # 2



STEP 7, # 2

STEP 8 - ADDITIONAL TIPS

1. For best results, replace your blade regularly. The blade needs to be replaced when the fabric begins to fray while cutting with Slice[™] Fabriqué.
2. For thicker materials, be sure to adjust your blade housing $\frac{3}{4}$ " of a turn to the left (counter-clockwise). This lowers the blade to allow Slice[™] Fabriqué to cut through thicker materials.

* Slice[™] now has a repositionable spray adhesive that works great with fabric (sold separately). It's easy to apply and dries immediately.